

Color shade		Product Name	Color Index No.	Physical data			Fastness						Recommended Application						
Full shade	Tint			PH value	Density	Oil absorption	Light	Heart	Water	Linseed Oil	Acid	Alkali	Water based ink	Solvent ink	Offset ink	Plastic & Rubber	Paint	Textile Paste	Stationery
		Permanent Red F2R	C.I.PR2	6.5-7.5	1.5	45-50	6	150	5	4	4	4	•	☉	☉		☉	•	☉
		Toluidine Red RN	C.I.PR3	7	1.4	40-50	7	180	4	5	3	3	☉				•		☉
		Permanent Red F4R-Y	C.I.PR8	6.5-7.5	1.6	40-50	5	160	4	4	5	4	☉		☉		☉	•	☉
		Permanent Red F4R-B	C.I.PR8	6.5-7.5	1.6	40-50	5	160	4	4	5	4	☉		☉		☉	•	☉
		Permanent Red FRLL	C.I.PR9	6.5-7.5	1.6	35-45	7	180	5	4	5	5	•		☉		☉	•	☉
		Permanent Red TRR	C.I.PR12	6.5-7.5	1.6	40-50	7	160	5	4	5	5	•		☉		☉	•	☉
		Toluidine Maroon 13	C.I.PR13	6.5-7.5	1.4	40-50	7	160	5	4	5	5					•		☉
		Fast Red 2R	C.I.PR21	6.5-7.5	1.6	40-50	7	150	4	3	5	5	•		☉		☉	•	•
		Brilliant Red -Y	C.I.PR22	6.5-7.5	1.6	45	5	160	4	4	5	5	•		☉		☉	•	☉
		Fast Rose Red	C.I.PR23	6.5-7.5	1.6	45	6	160	5	3	5	3	•		☉		☉	•	•
		Rubber Bordeaux BF	C.I.PR31	6.5-7.5	1.6	45	7	160	5	4	5	5	•				☉	•	☉
		Fast Red BBN	C.I.PR48:1	7-8.0	1.8	35-45	4	180	4	3	4	4	•	☉	•	☉	•	•	•
		Fast Red BBN	C.I.PR48:1	7-8.0	1.8	35-45	4	200	4	3	4	4	•	☉	☉	•	•	•	☉
		Brilliant Red BBC	C.I.PR48:2	7.5-8.5	1.6	45-50	4	180	5	3	4	4	•		☉	☉	☉	•	•
		Brilliant Red 2BXL	C.I.PR48:2	7.5-8.5	1.6	45-50	4	180	5	3	4	4		•			☉		
		Brilliant Red 2BP	C.I.PR48:2	7-8.0	1.6	45-50	4	220	5	3	4	4				•			
		Brilliant Red BBC	C.I.PR48:2	7-8.0	1.6	45-50	4	220	5	3	4	4	•	•	☉	☉			
		Brilliant Red BBC	C.I.PR48:2	7-8.0	1.6	45-50	4	220	5	3	4	4	☉	☉	☉	•	☉	☉	•
		Brilliant Red BBC	C.I.PR48:2	7-8.0	1.6	45-50	4	220	5	3	4	4	☉	☉	☉	•	☉	☉	☉

		Brilliant Red BBC	C.I.PR48:2	7-8.0	1.6	45-50	4	220	5	3	4	4				⊙	•		⊙
		Brilliant Red 2BP	C.I.PR48:2	7-8.0	1.6	45-50	4	240	5	3	4	4				•			
		Fast Red BBS	C.I.PR48:3	7-8.0	1.6	45-50	5	180	4	4	3	4	•		⊙	•	⊙	•	⊙
		Fast Red BBS	C.I.PR48:3	7-8.0	1.6	45-50	5	220	4	4	3	4	⊙	⊙	⊙	•	⊙	⊙	⊙
		Fast Red BBS-B	C.I.PR48:3	7-8.0	1.6	45-50	5	240	4	4	3	4				•			
		Permanent Red 2BM	C.I.PR48:4	7-8.0	1.6	45-50	6	180	4	5	3	4	•	⊙				•	⊙
		Lithol Scarlet Red-W	C.I.PR49:1	7-8.0	1.6	40-50	5	150	4	4	4	4	•	⊙	⊙		⊙	•	⊙
		Bronze Red C	C.I.PR53:1	7-8.0	1.6	45	5	160	4	4	4	3	•		•	⊙	⊙	⊙	•
		Bronze Red C-P	C.I.PR53:1	7-8.0	1.5	45	5	220	4	4	4	3				•			⊙
		Bronze Rubbine 4B	C.I.PR57:1	7-8.0	1.7	45	5	180	5	3	4	4		⊙	•		⊙		•
		Bronze Rubbine A6B	C.I.PR57:1	7-8.0	1.7	45	5	180	5	3	4	4			⊙	•	⊙		•
		Lithol Maroon	C.I.PR63:1	7-8.0	1.6	45	6	150	4	4	4	4	•		⊙		⊙	•	•
		Fast Pink Toner	C.I.PR81	6-7	1.7	45	5	150	4	4	5	4	•	•	⊙	⊙	⊙	•	⊙
		Fast Pink Lake	C.I.PR81	6-7	1.7	45	5	150	4	4	5	4	•	•	⊙	⊙	⊙	•	⊙
		Permanent Red FGR	C.I.PR112	6-7	1.5	30-40	7	160	5	4	5	5	•		⊙		•	•	⊙
		Permanent Red FBB	C.I.PR146	6-7	1.7	45	6	180	5	5	5	5	•	⊙	⊙	⊙	•	•	⊙
		Permanent Red FBB	C.I.PR146	6-7	1.7	45	6	180	5	5	5	5	•	•	•	•	⊙	⊙	⊙
		Permanent Red F5RK	C.I.PR170	6.5-7	1.5	40	7	180	5	5	5	5	•	⊙	•	⊙	•	•	⊙
		Permanent Red F7RK	C.I.PR170:1	6.5-7	1.5	40	7	180	5	5	5	5	•	⊙	•	•	•	•	⊙